Elliott Electric Supply

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

T101 40A 120V SPST Metal Indoor Time Clock

Intermatic Inc.

Catalog Number	T101
Manufacturer	Intermatic Inc.
Description	Metal Indoor Time Clock, 24 H Time Setting Mode, 1 No Contact Form, 24 H Time Setting, 125 V, 40 A, 1 Pole, Teeter Connection, -40 °F Operating Temperature, +130 °F Operating Temperature, 5 X 3 X 7-3/4 In Size, 2.5999 LB
Weight per unit	2.8 (lbs/each)
Product Category	Electromechanical Time Switche

Features

action	SPST
amperage rating	40
connection	Teeter Type
Contact Configuration	1 NO
Contact Rating	40 AMP @ 120 - 480 VAC (Resistive), 40 AMP @ 120 - 277 (Tungsten)
motor power	2 HP @ 120 VAC, 5 HP @ 240 VAC
Poles	1
Timing Range	0-24
Voltage Rating	125
Wattage	3

Descriptions

Description	40A 120V SPST METAL INDOOR TIME CLOCK
extra long description	INT-MAT T101 24-Hour Mechanical Tim

Manufacturer Information

GTIN	00078275000018
UPC	078275000018

Taxonomies, Classifications, and Categories

Category Description	TIME CLOCKS
Type	Electromechanical

Packaging

Carton	1
Package	12
Weight Per each	2.754

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Enclosure	NEMA 1
Frequency Rating	60
Mounting	WALL MOUNT
Operating Temperature	-40 to +130 DEG F, -40 to +54 DEG C
standard	cCSAus Certified, HVACR