

# Specifications



Photo is representative

## Eaton T20P11S2516

Eaton General purpose ventilated transformer, Aluminum windings, NEMA 2, 60 Hz, 220°C, 25 kVA, upright only , Single-phase, 240X480V, 120Y/240 Vac, NEMA ST-20, 1 at +5%, 150°C, 25 kVA, 240 X 480 Vac-120Y/240 Vac, WS45A, 3XA, DOE 2016

### General specifications

<b>PRODUCT NAME</b>	Eaton General purpose ventilated transformer
<b>CATALOG NUMBER</b>	T20P11S2516
<b>UPC</b>	786680147623
<b>PRODUCT LENGTH/DEPTH</b>	17 in
<b>PRODUCT HEIGHT</b>	33.5 in
<b>PRODUCT WIDTH</b>	22.5 in
<b>PRODUCT WEIGHT</b>	236 lb
<b>WARRANTY</b>	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>COMPLIANCES</b>	DOE2016 Efficient
<b>CERTIFICATIONS</b>	UL Listed
<b>CATALOG NOTES</b>	10 CFR Part 431 (2016) Efficient

## Physical Attributes

COIL MATERIAL	Aluminum
ENCLOSURE	NEMA 2
FRAME	FR842A
INSULATION	220 °C
MOUNTING	Floor or wall, upright only
TAP SIZE	1 at +5%, 2 at -5% x 2 at +2.5%, 4 at -2.5%
TYPE	Energy-efficient ventilated type DS-3 transformer
WIRING CONNECTION	3XA

## Miscellaneous

WEATHERSHIELD	WS45A
---------------	-------

## Performance Ratings

EFFICIENCY	10 CFR Part 431-2016 (DOE 2016)
FREQUENCY RATING	60 Hz
KVA RATING	25 kVA
PRIMARY VOLTAGE	240 V, 480 V
SECONDARY VOLTAGE	120Y/240 V
SOUND LEVEL	NEMA ST-20
TEMPERATURE RISE	150 °C rise
VOLT AMPERE RATING	25 kVA
VOLTAGE RATING	240 X 480 Vac-120Y/240 Vac

## Resources

BROCHURES	<a href="#">Eaton's low-voltage dry-type distribution transformers</a> <a href="#">Eaton's high-efficiency dry-type transformers</a>
SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - T20P11S2516</a>

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



### Eaton Corporation plc

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

