



\* Representative image

## T2535163S

by Acme Electric  
Catalog ID: T2535163S

Prop65\_Cancer&Reproductive

Low Voltage Distribution Transformer - Single Phase, 240X480 - 120/240V, 10kVA

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

## Product Details

### General

ANFC Taps	2
BNFC Taps	4
Construction	Encapsulated
Electrostatic Shield	Shielded
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Wall
Primary Voltage	240 X 480
Product Category	Dry Type Distribution Transformer
Secondary Voltage	120/240 V
Taps % Steps	2.5%
UL Insulation Class	180°C
UPC	047503734100
Winding Material	CU
kVA	10

### Dimensions

Height	15.19 in
Length	10.84 in
Weight	125 lb
Width	13.5 in

### Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	240 X 480 V

### Certifications and Compliance

CSA Standard	C22.2 No. 47
--------------	--------------

Nema Rating	NEMA 3R
UL Standard	UL 506