



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



TB35 1" Alu TB SR5 Conduit Body

Crouse-Hinds

Catalog Number	TB35
Manufacturer	Crouse-Hinds
Description	Conduit Outlet Body, Epoxy Powder Painted (Body); Natural (Gasket), 1 In Trade Size, 10.8 Cu.In Capacity, 90 ° Angle, 1 In Hub Size, 6.47 In Length, 2.77 In Width, 1.74 In Height, 0.53 LB/Ea
Weight per unit	0.5300 (lbs/each)
Product Category	Alum

Features

connection	Threaded / Set Screw
dimensions	6.4700 IN X 1.7400 IN X 2.7700 IN
Form	Series 5

Material, Color, and Finish

Color	Gray
-------	------

Dimensions and Weight

Hub Size	1 in
----------	------

Descriptions

Description	1" ALU TB SR5 CONDUIT BODY
extra long description	CRS-H TB35 1 RGD TB COND BODY AL
Features	Eaton's Crouse-Hinds Division Series 5 die cast copper-free aluminum conduit bodies, covers and gaskets are available for use with rigid or EMT conduit (with set screw). Conduit bodies are available in trade sizes 1/2" to 4", in the most popular conduit body shapes (C, LB, LL, LR, T) and 1/2" to 2" in TB and X shapes. The Series 5 family is available as components or pre-packaged in various configurations as a SnapPack assembly. In addition, Series 5 is completely interchangeable with other manufacturer

Manufacturer Information

Brand	EATON CROUSE-HINDS SERIES
GTIN	00662277008525
UPC	662277008525

Taxonomies, Classifications, and Categories

Category Description	HUB STYLE BOXES (GUAB, GUAT, ETC)
Type	Conduit outlet body



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	5
Weight Per each	0.53

Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - Other
Enclosure	Condulet
Mounting standard	Conduit UL, cUL