

Tamper-Resistant Floor Box Thermoplastic Cover, Light Almond

TM1542TRLA



Thermoplastic Cover Includes 15 amp 125 volt Decorator receptacle, matching detachable and replaceable hinged door; threaded device-mounting holes; drill guides for low-voltage poke-through holes; accepts any Decorator device; mounts on carpeting, hardwood, linoleum, tile floors; Four mounting/leveling screws. Light Almond.



features & benefits

- Tamper-Resistant shutters let plugs in, keep other things out.
- Hinged door is removable and easily replaceable.
- Durable construction, impact, and scratch resistant PVC construction.
- Standard Decorator opening that accepts GFCI, TVSS, DataCom, or other Decorator devices.
- Auto/Clamps and knockouts on both sides of box.
- Meets UL514(c) scrub water exclusion test.
- Threaded device mounting holes.
- Simple mounting box, fits into a 4 3/4 inch hole and mounts with 3 screws included.
- Ready for low-voltage wiring, drill guides on underside of cover.
- UL and cUL Listed.
- Captive screws on TM1542 Series -- screws will not be lost -- new.
- Made in USA.

specifications

General Info

Product Series: Slater
Component Type: Covers & Flanges

Listing Agencies/Third Party Information

CSA Listing Info: No

CUL Listing No: No
cULus: No
cURus: No
Federal Spec: No
UL Listing No: No
UN SPS C: 39121308
UR: No

Dimensions

Diameter U S: 6.5"

Technical Information

Material: Plastic
Floor Type: Wood

Buy American Act Compliance

Country of Origin: UNITED-STATES-OF-AMERICA
Buy American Act Status: Buy American Act Compliant