

Eaton TMCX200 2 L

Catalog Number: TMCX200 2 L

Eaton Crouse-Hinds series Terminator II TMCX cable gland, Liquid compound, Cable Range: 1.81-2.72", Cable Sealing: 2 (M), Metal-clad corrugated armoured, TECK armoured, armoured barrier and tray cable, Armoured gland, Aluminum, 2" NPT



General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series Terminator II TMCX cable gland	TMCX200 2 L
	UPC
	662276440296
Product Length/Depth	Product Height
6.88 in	4.98 in
Product Width	Product Weight
4.98 in	12.52 lb

Certifications and compliances

Area classification

Hazardous/Classified Locations

Standards type

NEC/CEC

NEC hazardous rating

Class I, Division 1

Class II, Division 1

Class III

NEMA Rating

4X

Product specifications

Protection type

Explosion-proof

Cable type

TECK armoured

Tray cable

Metal-clad with interlocked or continuously welded corrugated armoured

Armoured barrier

Gland type

Armoured

Thread Size

2"

Thread type

NPT

Cable sealing range

2 (M)

Cable range (min/max)

1.81-2.72"

Material

Aluminum

Barrier type

Liquid Compound

Resources

Brochures

[Crouse-Hinds series TMCX II brochure](#)

[Crouse-Hinds series Chico LiquidSeal flyer](#)

Catalogs

[Crouse-Hinds series TMCX II catalog page](#)

Certification reports

[TMCX II Explosionproof Armoured Barrier and Non-armoured Barrier](#)

[Gland UL certification](#)

[TMCX II Explosionproof Armoured Barrier and Non-armoured Barrier](#)

[Gland Canadian certification](#)

Installation instructions

IF 1647B - TMCX Terminator II Cable Gland

IF 1647 - TMCX Terminator II Cable Gland

Specifications and datasheets

Eaton Specification Sheet - TMCX200 2 L



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)