

# Eaton TMCX7247

Catalog Number: TMCX7247

Eaton Crouse-Hinds series TMCX cable gland, Metal-clad corrugated, TECK armoured and tray cable, Armoured barrier and non-armoured barrier, Aluminum, Outer Sheath: 1.99-2.72", 2-1/2" NPT, Armor Range: 1.93-2.47"



## General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series TMCX cable gland	TMCX7247
	UPC
	782274414737
Product Length/Depth	Product Height
7.5 in	4 in
Product Width	Product Weight
4 in	4.65 lb

## Certifications and compliances

### Area classification

Hazardous/Classified Locations

### Standards type

NEC/CEC

### NEC hazardous rating

Class I, Division 1

Class II, Division 1

Class III

### NEMA Rating

4

## Product specifications

### Protection type

Explosion-proof

### Cable type

Metal-clad with interlocked or continuously welded corrugated armoured

TECK armoured

Tray cable

### Gland type

Armoured Barrier and Non-armoured Barrier

### Material

Aluminum

### Thread Size

2-1/2"

### Thread type

NPT

### Armor (min/max)

1.93-2.47"

### Outer sheath (min/max)

1.99-2.72"

## Resources

### Catalogs

[Crouse-Hinds series TMCX catalog page](#)

### Certification reports

[TMCX Explosionproof Armoured Barrier Gland UL certification](#)

### Installation instructions

[IF 1184 - TMCX Terminator Cable Fittings](#)

### Specifications and datasheets

[Eaton Specification Sheet - TMCX7247](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)