



One Hole Straps PC 5160

One Hole Straps are used to secure cables, tubing, pipe or E.M.T. to a surface

- Zinc Plated Steel (After Fabrication)
- Inverted Rib For Strength
- For E.M.T. / Pipe

CAT NO	UPC	TYPE	SIZE	GAUGE	STD	MSTR	WT/STD	UNIT
TW14	27745	Coaxial	1/4"	18 GA	100	1000	0.57#	C
TW38	27750	BX *	3/8"	18 GA	100	1000	1.15#	C
TW501	27700	E.M.T.	1/2"	18 GA	100	1000	2.22#	C
TW75	27705		3/4"	18 GA	100	1000	3.12#	C
TW100	27710		1"	18 GA	100	500	3.45#	C
TW125	27715		1-1/4"	15 GA	100	500	5.49#	C
TW150	27720		1-1/2"	15 GA	50	500	3.86#	C
TW200	27725		2"	13 GA	50	500	7.10#	C
TW250	27726	E.M.T. / Pipe	2-1/2"	9 GA	25	100	10.13#	C
TW300	27727		3"	9 GA	25	100	13.38#	C
TW350	27728		3-1/2"	7 GA	25	100	16.61#	C
TW400	27729		4"	7 GA	25	100	19.02#	C
MTW50	27730	E.M.T.	1/2"	14 GA	100	1000	3.62#	C
MTW75	27735	Medium	3/4"	14 GA	100	1000	4.17#	C
MTW100	27740	Weight	1"	14 GA	100	500	5.45#	C
HW50	27800	Pipe	1/2"	18 GA	100	1000	2.53#	C
HW75	27805		3/4"	18 GA	100	1000	3.19#	C
HW100	27810		1"	14 GA	100	1000	6.66#	C
HW125	27815		1-1/4"	13 GA	50	500	5.49#	C
HW150	27820		1-1/2"	11 GA	50	500	8.36#	C
HW200	27825		2"	11 GA	50	500	10.66#	C
MHW50	27830	Pipe	1/2"	14 GA	100	1000	3.82#	C
MHW75	27835	Medium	3/4"	14 GA	100	1000	5.00#	C
MHW100	27840	Weight	1"	14 GA	100	1000	6.71#	C

* Accommodates 12-2, 12-3, 10-2, 10-3 BX



Two Hole Straps PC 5200

Two hole straps are used to secure cables, tubing, pipe or E.M.T. to a surface

- Zinc Plated Steel (After Fabrication)
- Inverted Rib For Strength
- For E.M.T. / Pipe

CAT NO	UPC		SIZE	GAUGE	STD	MSTR	WT/STD	UNIT
TW301	27300	E.M.T.	1/2"	22 GA	250	1000	4.13#	C
TW302	27305		3/4"	22 GA	250	1000	4.67#	C
TW303	27310		1"	22 GA	250	1000	8.24#	C
TW304	27315		1-1/4"	20 GA	100	500	4.45#	C
TW305	27320		1-1/2"	20 GA	100	500	4.83#	C
TW306	27325		2"	20 GA	50	250	3.11#	C
HW400	27900	Pipe	3/8"	22 GA	250	1000	4.64#	C
HW401	27905		1/2"	22 GA	250	1000	4.70#	C
HW402	27910		3/4"	22 GA	250	1000	5.33#	C
HW403	27915		1"	20 GA	100	1000	3.82#	C
HW404	27920		1-1/4"	20 GA	100	500	4.74#	C
HW405	27925		1-1/2"	20 GA	100	500	5.30#	C
HW406	27930		2"	18 GA	50	500	4.32#	C
HW407	27935		2-1/2"	15 GA	25	250	4.96#	C
HW408	27940		3"	15 GA	25	250	5.64#	C
HW409	27945		3-1/2"	15 GA	10	50	3.44#	C
HW410	27950	4"	15 GA	10	50	3.72#	C	