

# Eaton UASTS61C224CH

Catalog Number: UASTS61C224CH

Eaton meter socket, Instrument rated socket, 20A, Over/under, 3-5/16 inch hub cover plate, Six-jaw, 1-ph, Factory wired test switch, Gnd conn (#14-#2 Cu), Al, Triplex, 3-wire, Ringless, 600 Vac

## General specifications



Photo is representative

**Product Name**

Eaton meter socket

**UPC**

786685216386

**Product Height**

20 in

**Product Weight**

15 lb

**Catalog Number**

UASTS61C224CH

**Product Length/Depth**

4.359 in

**Product Width**

12 in

**Warranty**

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

**Certifications**

UL Listed

Type

Instrument rated socket

Amperage Rating

20A

Feed type

Top/bottom

Number of jaws

Six-jaw

Phase

Single-phase

Enclosure material

Aluminum

Number of wires

Three-wire

Hub type

3-5/16 in hub cover plate

Security

Ringless

Voltage rating

600 V

Accessories

Factory wired test switch

Number of sockets

1

Brochures

[Single Meter Sockets](#)

Drawings

[Dimensional Drawing - SKT/SW 20A 6T FW HCP](#)

Specifications and datasheets

[Eaton Specification Sheet - UASTS61C224CH](#)

# Eaton UASTS61C224CH

Catalog Number: UASTS61C224CH

Eaton meter socket, Instrument rated socket, 20A, Over/under, 3-5/16 inch hub cover plate, Six-jaw, 1-ph, Factory wired test switch, Gnd conn (#14-#2 Cu), Al, Triplex, 3-wire, Ringless, 600 Vac

## General specifications



Photo is representative

**Product Name**

Eaton meter socket

**UPC**

786685216386

**Product Height**

20 in

**Product Weight**

15 lb

**Catalog Number**

UASTS61C224CH

**Product Length/Depth**

4.359 in

**Product Width**

12 in

**Warranty**

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

**Certifications**

UL Listed

defaultTaxonomyAttributeLabel

Type

Instrument rated socket

Amperage Rating

20A

Feed type

Top/bottom

Number of jaws

Six-jaw

Phase

Single-phase

Enclosure material

Aluminum

Number of wires

Three-wire

Hub type

3-5/16 in hub cover plate

Security

Ringless

Voltage rating

600 V

Accessories

Factory wired test switch

Number of sockets

1

Resources

Brochures

[Single Meter Sockets](#)

Drawings

[Dimensional Drawing - SKT/SW 20A 6T FW HCP](#)

Specifications and datasheets

[Eaton Specification Sheet - UASTS61C224CH](#)