

Vynckier Enclosure Systems, Inc.
249 McCarty Drive • Houston, Texas 77029
Telephone: (713) 374-7850 • Fax: (800) 444-1261
E-Mail: • Web site: www.EnclosuresOnline.com

[All Categories](#) > [VJ Series Enclosure with Stainless Steel Twist Latch\(s\) and a Stainless Steel Piano Hinge](#) > [VJ Series Enclosure with Stainless Steel Padlockable Latch\(s\) and a Stainless Steel Piano Hinge](#) > [Item # VJ1412HWPL2](#)

Item # VJ1412HWPL2 VJ Series Enclosure with Stainless Steel Padlockable Latch(s) and a Stainless Steel Piano Hinge
\$147.8365

VJ Series Enclosure with Stainless Steel Padlockable Latch(s) and a Stainless Steel Piano Hinge

- All VJ Series enclosures are designed to meet the Joint Industrial Council (JIC) standards in the United States.
- VJ's are made from corrosion resistant hot compression molded fiberglass reinforced polyester and do not contain halogens.
- The VJ series "HWPL" enclosures include one or two stainless steel padlockable latches to secure one side of the cover to the base and a stainless steel piano hinge that secures the other. Rivets connect the hinge to the cover and self-tapping screws connect the screws to the base.
- Seven sizes are available from 6 x 6 inch to 18 x 16 inch
- Vynckier's VJ enclosures are capable of withstanding continuous temperatures from -58 °F (-50°C) up to 302 °F (150 °C).
- VJ enclosures provide protection for equipment and operators from indirect electrical contact.
- All VJ enclosures are UL listed per UL Standard 508 for NEMA 3, 3R, 4, 4X, 12 and 13; CSA Certified per Standard C22.2-0, 0.4, 0.7, 0.6, 94 Type 3, 3R, 4, 4X, 12 and 13.



[larger image](#)



[larger image](#)

Specifications

FRP UL Type Rating	3, 3R, 4, 4X, 12, 13
Temperature Resistance (° F)	-58 to +302
Temperature Resistance (° C)	-50 to +150
Outside Height (inch)	15.32
Outside Height (mm)	389
Outside Width (inch)	13.30
Outside Width (mm)	338
Outside Depth (inch)	6.70
Outside Depth (mm)	170.0
Inside Dim. A (inch)	14.00

Inside Dim. A (mm)	355.6
Inside Dim. B (inch)	12.00
Inside Dim. B (mm)	304.8
Inside Dim. C (inch)	5.82
Inside Dim. C (mm)	147.8
Weight (lbs)	8.6
Weight (kg)	3.90
Mounting Plate Part No. (Aluminum Steel Non-Metallic)	MP1412A MP1412N MP1412S
Dim. Mounting Plate (inch)	12.75 x 10.88
Dim. Mounting Plate (mm)	324 x 276
Front Panel - Plain	VFP1412A
Front Panel - Hinged	VFPH1412A
Dim. E (inch)	1.75
Dim. E (mm)	44.4
Dim. F (inch)	4.92
Dim. F (mm)	125.0
Dim. I (inch)	0.50
Dim. I (mm)	12.7
Dim. J (inch)	14.75
Dim. J (mm)	374.6
Dim. K (inch)	10.00
Dim. K (mm)	254.0
Dim. L (inch)	0.31
Dim. L (mm)	8.0
Dim. M (inch)	0.12
Dim. M (mm)	3.0
Dim. N (inch)	15.51
Dim. N (mm)	394.0
Dim. O (inch)	10.24
Dim. O (mm)	260.0
Dim. P (inch)	12.26
Dim. P (mm)	311.5
Dim. Q (inch)	0.08
Dim. Q (mm)	2.0
Dim. R (inch)	6.40
Dim. R (mm)	162.5
Latch Spacing (inch)	9.56
Latch Spacing (mm)	243
UPC Code	635394013253
Availability	Stock
Shipment in Days	1

Vynckier Enclosure Systems, Inc.
249 McCarty Drive • Houston, Texas 77029
Telephone: (713) 374-7850 • Fax: (800) 444-1261
E-Mail: • Web site: www.EnclosuresOnline.com

[All Categories](#) > [VJ Series Enclosure with Stainless Steel Twist Latch\(s\) and a Stainless Steel Piano Hinge](#) > [VJ Series Enclosure with Stainless Steel Padlockable Latch\(s\) and a Stainless Steel Piano Hinge](#) > [Item # VJ1412HWPL2](#)

Item # VJ1412HWPL2 VJ Series Enclosure with Stainless Steel Padlockable Latch(s) and a Stainless Steel Piano Hinge
\$147.8365

VJ Series Enclosure with Stainless Steel Padlockable Latch(s) and a Stainless Steel Piano Hinge

- All VJ Series enclosures are designed to meet the Joint Industrial Council (JIC) standards in the United States.
- VJ's are made from corrosion resistant hot compression molded fiberglass reinforced polyester and do not contain halogens.
- The VJ series "HWPL" enclosures include one or two stainless steel padlockable latches to secure one side of the cover to the base and a stainless steel piano hinge that secures the other. Rivets connect the hinge to the cover and self-tapping screws connect the screws to the base.
- Seven sizes are available from 6 x 6 inch to 18 x 16 inch
- Vynckier's VJ enclosures are capable of withstanding continuous temperatures from -58 °F (-50°C) up to 302 °F (150 °C).
- VJ enclosures provide protection for equipment and operators from indirect electrical contact.
- All VJ enclosures are UL listed per UL Standard 508 for NEMA 3, 3R, 4, 4X, 12 and 13; CSA Certified per Standard C22.2-0, 0.4, 0.7, 0.6, 94 Type 3, 3R, 4, 4X, 12 and 13.



[larger image](#)



[larger image](#)

Specifications

FRP UL Type Rating	3, 3R, 4, 4X, 12, 13
Temperature Resistance (° F)	-58 to +302
Temperature Resistance (° C)	-50 to +150
Outside Height (inch)	15.32
Outside Height (mm)	389
Outside Width (inch)	13.30
Outside Width (mm)	338
Outside Depth (inch)	6.70
Outside Depth (mm)	170.0
Inside Dim. A (inch)	14.00

Inside Dim. A (mm)	355.6
Inside Dim. B (inch)	12.00
Inside Dim. B (mm)	304.8
Inside Dim. C (inch)	5.82
Inside Dim. C (mm)	147.8
Weight (lbs)	8.6
Weight (kg)	3.90
Mounting Plate Part No. (Aluminum Steel Non-Metallic)	MP1412A MP1412N MP1412S
Dim. Mounting Plate (inch)	12.75 x 10.88
Dim. Mounting Plate (mm)	324 x 276
Front Panel - Plain	VFP1412A
Front Panel - Hinged	VFPH1412A
Dim. E (inch)	1.75
Dim. E (mm)	44.4
Dim. F (inch)	4.92
Dim. F (mm)	125.0
Dim. I (inch)	0.50
Dim. I (mm)	12.7
Dim. J (inch)	14.75
Dim. J (mm)	374.6
Dim. K (inch)	10.00
Dim. K (mm)	254.0
Dim. L (inch)	0.31
Dim. L (mm)	8.0
Dim. M (inch)	0.12
Dim. M (mm)	3.0
Dim. N (inch)	15.51
Dim. N (mm)	394.0
Dim. O (inch)	10.24
Dim. O (mm)	260.0
Dim. P (inch)	12.26
Dim. P (mm)	311.5
Dim. Q (inch)	0.08
Dim. Q (mm)	2.0
Dim. R (inch)	6.40
Dim. R (mm)	162.5
Latch Spacing (inch)	9.56
Latch Spacing (mm)	243
UPC Code	635394013253
Availability	Stock
Shipment in Days	1