



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



WG157310D PF1202T Rep Motor *Intermatic Inc.*

Catalog Number	WG157310D
Manufacturer	Intermatic Inc.
Description	208-277 Vac, 60 HZ Motor For T102, T104, T106, T172, T174, WH40
Weight per unit	0.2000 (lbs/each)
Product Category	Time Switch Accessories

Features

for use with	T100, T102, T104, T170, T180, T100R201, T1400, T100-20, T100R301, and WH10, WH30, WH40 Series Mechanical Time Switches
Voltage Rating	208 to 277
Wattage	3

Descriptions

Description	PF1202T REP MOTOR
extra long description	INT-MAT WG1573-10D 208-277 VAC, 60
Long Description	208-277 VAC, 60 Hz Motor for T102, T104, T106, T172, T174, WH40
Product Type	208-277 Vac, 60 HZ Motor For T102, T104, T106, T172, T174, W
Special Features	Features: Very sturdy with a high Torque, Fixed tab connectors easily slip over the timer connection poles for simple installation

Manufacturer Information

Brand	Intermatic
GTIN	00078275020122
Manufacturers Part Number	WG1573-10D
UPC	078275020122

Taxonomies, Classifications, and Categories

Category Description	Fuses & Fuse Accessories
Type	Clock Motor

Packaging

Carton	1
Weight Per each	0.2

Uses, Certifications, and Standards

Frequency Rating	60
standard	CSA Certified, UL Recognized