



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

5575 Ruben M Torres Blvd  
78526-0000, TX Brownsville  
Phone: 956-295-3007  
Fax: 956-295-3008



## WT6B Wiretwist Wire Connector, WT6 Red, 250/Bag

*Ideal*

Catalog Number	WT6B
Manufacturer	Ideal
Description	Buchanan, Wire Connector, Wiretwist, Conductor Range: 18 - 8 Awg, 2/14 Awg Min, 4/12 Awg Max, Number Of Conductors: 1 to 5, Material: Flame-Retardant Polypropelene, Color: Red, Voltage Rating: 600 V, Environmental Conditions: Tough, UI 94V-2 Flame-Retardant Shell Rated At 105 Deg C (221 F), Model Number: WT6
Weight per unit	0.0060 (lbs/each)
Product Category	Electrical Fixture Conn ( Nuts

### Features

Material	Flame-retardant Polypropelene
Voltage Rating	600

### Material, Color, and Finish

Color	Red
-------	-----



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

5575 Ruben M Torres Blvd  
78526-0000, TX Brownsville  
Phone: 956-295-3007  
Fax: 956-295-3008

## Descriptions

Description	WIRETWIST WIRE CONNECTOR, WT6 RED, 250/BAG
extra long description	IDEAL WT6-B WIRE-TWIST CONN.,RED,BA
Features	With five, color-coded connectors designed to accommodate hundreds of different solid or stranded wire combinations, WireTwist Wire Connectors offer an economical connector that brings a lot of value in comfort and performance. The fixed, live-action, square-wire spring threads itself as it draws wires into the connector, creating a secure pressure grip. The rugged, thermoplastic shell withstands extreme environments. The deep, wide-throated skirt protects against flashover and turned back strands providing
Long Description	Buchanan, Wire Connector, WireTwist, Conductor Range: 18 - 8 AWG, 2/14 AWG Min, 4/12 AWG MAX, Number Of Conductors: 1 to 5, Material: Flame-retardant Polypropelene, Color: Red, Voltage Rating: 600 V, Environmental Conditions: Tough, UL 94V-2 Flame-Retardant Shell Rated At 105 DEG C (221 F), Model Number: WT6
Product Type	Wire-Twist Conn., Red, Bag 250
Special Features	1,000V Maximum In Fixtures And Signs;Deep, Wide-Throated Skirt Protects Against Flash-Over And Turned-Back Strands For Maximum Dielectric Protection;Features: Five Color-Coded Models Cover Common Construction Wire Ranges;Fixed, Square-Wire Spring Threads Itself Creating A Secure Pressure Grip;Model Number: WT6;Ribbed Cap Provides Positive Grip For Fast, Easy Installation;Tough, UL 94V-2 Flame-Retardant Shell Rated At 105 Degree C (221 Degree F);UL 486C Listed And CSA 22.2 #188 Certified

## Manufacturer Information

Brand	Buchanan
GTIN	00781789610092
Manufacturers Part Number	WT6-B
UPC	781789610092

## Taxonomies, Classifications, and Categories

Category Description	WIRE NUTS
----------------------	-----------

## Availability

minimum qty	250
-------------	-----

## Packaging

Carton	5000
Weight Per each	0.006



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

5575 Ruben M Torres Blvd  
78526-0000, TX Brownsville  
Phone: 956-295-3007  
Fax: 956-295-3008

## Uses, Certifications, and Standards

Application	Insulating or Joining 1 or more conductors
environmental conditions	Tough, UL 94V-2 Flame-Retardant Shell Rated At 105 DEG C (221 F)
standard	CSA C22.2 #188, UL 486C Listed, RoHS