

# Specifications



## Eaton XBUT4FBEL24

Eaton XB IEC terminal block, Screw Connection Fuse Terminal Blocks, for 5 x 20 mm Fuse, Black, 10 AWG/4 mm<sup>2</sup> maximum wire, With LED 12–30V, 1–2.5 mA light

### General specifications

<b>PRODUCT NAME</b>	Eaton XB IEC terminal block
<b>CATALOG NUMBER</b>	XBUT4FBEL24
<b>UPC</b>	782116905225
<b>PRODUCT LENGTH/DEPTH</b>	1.85 in
<b>PRODUCT HEIGHT</b>	2.17 in
<b>PRODUCT WIDTH</b>	0.24 in
<b>PRODUCT WEIGHT</b>	0.04 lb
<b>WARRANTY</b>	1 year
<b>CERTIFICATIONS</b>	CSA Certified UL Listed



Powering Business Worldwide

## Product specifications

<b>SPECIAL FEATURES</b>	With LED 12–30V, 1–2.5 mA light
-------------------------	---------------------------------

<b>TYPE</b>	IEC-XB Series
-------------	---------------

<b>AMPERAGE RATING</b>	6.30A (IEC), 6.30A (UL)
------------------------	-------------------------

<b>VOLTAGE RATING</b>	UL 600V
-----------------------	---------

## Resources

<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Eaton Specification Sheet - XBUT4FBEL24</a>
--------------------------------------	---

---

**PROJECT NAME:**

---

**PROJECT NUMBER:**

---

**PREPARED BY:**

---

**DATE:**

---



### Eaton Corporation plc

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

