

Specifications



Photo is representative



Eaton XTCE032C01B

Eaton XT IEC contactor, 32A, 220 Vac 50 Hz, 240 Vac 60 Hz, 1NC, 32A, Frame C, 45 mm, 50-60 Hz, 3, 5, 5/ 10, 10, 20, 25 hp (1/3PH @115, 200, 230/200, 230, 460, 575 V), Three-pole, Screw terminals, Full voltage non-reversing contactor

General specifications

PRODUCT NAME	Eaton XT IEC contactor
CATALOG NUMBER	XTCE032C01B
UPC	782116485901
PRODUCT LENGTH/DEPTH	3.425 in
PRODUCT HEIGHT	3.898 in
PRODUCT WIDTH	1.85 in
PRODUCT WEIGHT	0.9 lb
WARRANTY	1 year
COMPLIANCES	RoHS Compliant CE Marked
CERTIFICATIONS	IEC 60947 EN 60947 UL Listed CSA Certified
CATALOG NOTES	Screw terminals (6-65A); 5 mm (80-150A); no lugs (185-2000A)



Powering Business Worldwide

Product specifications

AMPERAGE RATING	32A
HP RATING - MAX	3, 5, 5/ 10, 10, 20, 25 hp (1/3PH @115,200,230/200,230,460,575 V)
NUMBER OF POLES	Three-pole
TYPE	Full voltage non-reversing contactor
FREQUENCY RATING	50-60 Hz
FRAME SIZE	45 mm
TERMINALS	Screw terminals
COIL VOLTAGE	220-240 Vac, 50/60 Hz
CONTACT CONFIGURATION	1 NC
CONTINUOUS AMPERE RATING	32 A
SERIES	XT IEC
OPERATION	Non-reversing

Resources

CATALOGS	Motor Control and Protection, IEC Contactors and Starters, Volume 5, Tab 1
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - XTCE032C01B

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

