

# Compression Terminal

By Burndy  
Catalog # [YA392LN](#)

750 kcmil CU, Two Hole, 1/2 Stud Size, 1-3/4 Hole Spacing, Standard Barrel, Inspection Window, Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, Black Color Code, 24 Die Index.



## Application

Wire Termination

## General

Color Code	Black
Connector Type	STANDARD BARREL
Die Index	24
EU RoHS Indicator	Yes
Feature - Barrel Style	<ul style="list-style-type: none"> <li>• Chamfered</li> <li>• Skived</li> </ul>
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	2
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810522073

## Dimensions

Dimension - B Length fraction	1-7/16 in
Dimension - B Length inch	1.42 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Dimension - Bolt Size inch	0.5
Dimension - D inch	3.02 in
Dimension - Hole Size fraction	1/2
Dimension - Hole Size inch	0.56
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	136 mm
Dimension - Length Overall inch	5.36 in
Dimension - N inch	0.63 in
Dimension - Outside Diameter inch	1.30 in
Dimension - Pad Width inch	1.91 in
Dimension - Strip Length inch	1-15/16
Dimension - Stud Size fraction	1/2

## Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

## Conductor Related

Conductor - Copper Str Size	750 KCMIL
Conductor - Copper Str Size Range	750 kcmil
Conductor - Material	COPPER
Conductor Size	750 KCMIL
Conductor Type	CODE

## Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Carton Quantity	6
Minimum Pack Quantity	1

## Product Assets

- [Catalogs - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - Copper Code Standard Terminals Tooling and Installation Instructions](#)
- [Sales Drawings - SD035209-13](#)
- [Video - HYDENT Compression Terminal Overview Video](#)

Dimension - Stud Size inch	1/2
Dimension - Z inch	0.64 in
Physical Attribute - Tongue Angle	Straight



**A proud member of the Hubbell Family.**

©2023 Hubbell Incorporated. All rights reserved.  
BRDY-YA392LN-SPEC-EN | REV 6/2023