

Eaton UT4R2352TCH

Catalog Number: UT4R2352TCH

Eaton meter socket, Multi position commercial or resi service, 200A, Over/under, 5x5 inch hub open, #1/0-500 kcmil, 4-jaw, 1-ph, #8-250 kcmil, Gnd conn (#14-#2 Cu), Triplex, 3-wire, Ringless, 600 Vac

General specifications



Product Name

Eaton meter socket

Catalog Number

UT4R2352TCH

UPC

782116016693

Product Length/Depth

5.38 in

Product Height

14.13 in

Product Width

40.63 in

Product Weight

40 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL Listed

defaultTaxonomyAttributeLabel

Type

Multiple position commercial or residential service

Amperage Rating

200A

Feed type

Top/bottom

Number of jaws

Four-jaw

Phase

Single-phase

Utility approvals

ME : Central Maine Power

GA : Georgia Power

NM : Texas-New Mexico Power (TNMP)

TX : Texas-New Mexico Power (TNMP)

SC : South Carolina Electric and Gas (SCE&G)

TX : Entergy

Line

#1/0-500 kcmil

Load

#8-250 kcmil

Number of wires

Three-wire

Hub type

5 x 5 hub opening

Security

Ringless

Voltage rating

600 V

Number of sockets

4

Resources

Catalogs

Eaton's Volume 1—Residential and Light Commercial

Drawings

Dimensional Drawing - SKT/4 GANG 200A 1P HO

Specifications and datasheets

Eaton Specification Sheet - UT4R2352TCH

Metering Equipment - Utilities Servicing Illinois, Iowa, Kansas, Missouri, Oklahoma and Wisconsin



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)