ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

GE232MAXNULTRA 2LIGHT 4' Dual Voltage Ballast

Ge By Current Lamps

Catalog Number	GE232MAXNULTRA
Manufacturer	Ge By Current Lamps
Description	Ge Ultramax™, 60 HZ, Normal Ballast Factor, Instant Start, 9.5 In Length, 1.3 In Width, 1 In Height, 2 or 1 F32T8
Weight per unit	1.1 (lbs/each)
Product Category	Electronic Linear Fluorescent

Features

Ballast Factor	Normal
start type	Instant Start

Dimensions and Weight

Height	1.0
Length	9.5
Width	1.3

Descriptions

Description	2LIGHT 4' DUAL VOLTAGE BALLAST
extra long description	GEL GE232MAXPN/ULTRA 72266 ELECTRON
Long Description	GE UltraMax™, 60 Hz, Normal Ballast Factor, Instant Start, 9.5 IN Length, 1.3 IN Width, 1 IN Height, 2 or 1 F32T8
Product Type	72266 Electronic Ballast
Special Features	GE232MAXP-N/ULTRA (replaces GE232MAX-N/ULTRA) Designation

Manufacturer Information

Brand	Ge Traditional Lamps
GTIN	00043168722667
Manufacturers Part Number	GE232MAXPN/ULTRA
UPC	043168722667

Taxonomies, Classifications, and Categories

Category Description	Fluorescent
Type	Ballasts_Fluorescent_Electronic

Packaging

Carton	1
Weight Per each	1.1

Uses, Certifications, and Standards

Frequency Rating	60.0