

GE energy smart® LED replacement lamps

Directional Lamps (PAR)

Bulb Shape	Base Type	Watts	Order Code	Description	Volts	Case Qty**	MOL (In)	Lumens Initial	CBCP	Initial Color Temp	CRI	Wattage Equivalent	*Rated Life L70 (Hrs)	Dimmable	ENERGY STAR® Status	#Location Rating	Additional Information
Compact PAR16																	
	MED	4	75626	LED4P16/NFL/CD	120	3	2.87	100	230	3000	82	-	15,000	-		Dry	Accent, 30° beam, Black
			75848	LED4P16S830/30	120	6	2.87	100	230	3000	80	-	15,000	-		Dry	Accent, 30° beam, Silver
			78351	LED4P16S/NFL/TP	120	3	2.87	100	230	3000	82	-	15,000	-		Dry	Accent, 30° beam, Silver
		4.5	62905	LED5P16S/NFL/TP	120	3	2.87	200	800	3000	82	35W	25,000	-	★	Dry	Accent, 25° beam, Silver
			64886	LED5P16S830/25	120	6	2.87	200	800	3000	82	35W	25,000	-	★	Dry	Accent, 25° beam, Silver
			66136	LED5DP16S/NFL/TP	120	3	3.00	180	560	3000	80	25W	25,000	Yes		Dry	Accent, 25° beam, Silver
Compact PAR 20																	
	MED	7	61915	LED7DP20B830/12	120	6	3.55	330	3400	3000	81	50W	50,000	Yes	★	Damp	Accent, 12° beam, Black
			61916	LED7DP20B830/20	120	6	3.55	330	2070	3000	80	50W	50,000	Yes	★	Damp	Accent, 20° beam, Black
			61917	LED7DP20B827/20	120	6	3.55	300	1900	2700	80	50W	50,000	Yes	★	Damp	Accent, 20° beam, Black
			61918	LED7DP20W830/12	120	6	3.55	330	3400	3000	81	50W	50,000	Yes	★	Damp	Accent, 12° beam, White
			61919	LED7DP20W830/20	120	6	3.55	330	2070	3000	80	50W	50,000	Yes	★	Damp	Accent, 20° beam, White
			61920	LED7DP2W827/20	120	6	3.55	300	1900	2700	80	50W	50,000	Yes	★	Damp	Accent, 20° beam, White
			61921	LED7DP20S830/20	120	6	3.55	330	2070	3000	80	50W	50,000	Yes	★	Damp	Accent, 20° beam, Silver
			64494	LED7DP20S827/20	120	6	3.55	300	1900	2700	80	50W	50,000	Yes	★	Damp	Accent, 20° beam, Silver
			63696	LED7DP20B827/15	120	6	3.55	300	3400	2700	80	50W	50,000	Yes	★	Damp	Accent, 15° beam, Black
			67578	LED7DP20B827/35	120	6	3.55	300	840	2700	80	50W	25,000	Yes		Damp	Accent, 35° beam, Black
			63023	LED7DP20S/NFL/TP	120	3	3.55	300	1900	2700	80	50W	50,000	Yes	★	Damp	Accent, 20° beam, Silver
Compact PAR 30 - Low Glare - Visual Comfort Lens™																	
	MED	12	67922	LED12DP30R930/15	120	6	3.75	860	5650	3000	91	65W	25,000	Yes	★	Dry	Accent, 15° beam, Silver
			67923	LED12DP30R930/25	120	6	3.75	860	3100	3000	91	75W	25,000	Yes	★	Dry	Accent, 25° beam, Silver
			67924	LED12DP30R930/40	120	6	3.75	860	1350	3000	91	75W	25,000	Yes	★	Dry	Accent, 40° beam, Silver
			67925	LED12DP30R927/15	120	6	3.75	820	5350	2700	91	65W	25,000	Yes	★	Dry	Accent, 15° beam, Silver
			67926	LED12DP30R927/25	120	6	3.75	820	2950	2700	91	75W	25,000	Yes	★	Dry	Accent, 25° beam, Silver
			67927	LED12DP30R927/40	120	6	3.75	820	1300	2700	91	65W	25,000	Yes	★	Dry	Accent, 40° beam, Silver
Compact PAR 30 Long Neck - Low Glare - Visual Comfort Lens™																	
	MED	12	66050	LED12P3LS930/25	120	6	4.75	660	3000	3000	92	75W	25,000	-	★	Dry	Narrow Flood, 25° beam, Silver
			66052	LED12P3LS927/25	120	6	4.75	630	3000	2700	92	75W	25,000	-	★	Dry	Narrow Flood, 25° beam, Silver
			66053	LED12P3LS927/40	120	6	4.75	630	900	2700	92	50W	25,000	-	★	Dry	Flood, 40° beam, Silver
			68387	LED12DP3LR930/15	120	6	4.75	860	5650	3000	91	65W	25,000	Yes	★	Dry	Accent, 15° beam, Silver
			68388	LED12DP3LR930/25	120	6	4.75	860	3100	3000	91	75W	25,000	Yes	★	Dry	Accent, 25° beam, Silver
			68389	LED12DP3LR930/40	120	6	4.75	860	1350	3000	91	75W	25,000	Yes	★	Dry	Accent, 40° beam, Silver
			68390	LED12DP3LR927/15	120	6	4.75	820	5350	2700	91	65W	25,000	Yes	★	Dry	Accent, 15° beam, Silver
			68391	LED12DP3LR927/25	120	6	4.75	820	2950	2700	91	75W	25,000	Yes	★	Dry	Accent, 25° beam, Silver
			68392	LED12DP3LR927/40	120	6	4.75	820	1300	2700	91	65W	25,000	Yes	★	Dry	Accent, 40° beam, Silver
Compact PAR30																	
	MED	10	61922	LED10DP30S830/20	120	6	3.75	500	3720	3000	80	60W	50,000	Yes	★	Damp	Accent, 20° beam, Silver
			61923	LED10DP30S827/20	120	6	3.75	450	3450	2700	80	55W	50,000	Yes	★	Damp	Accent, 20° beam, Silver
			68013	LED10DP30S827/35	120	6	3.75	450	1240	2700	80	55W	25,000	Yes	★	Damp	Accent, 35° beam, Silver
			64326	LED10DP30W827/20	120	6	3.75	450	3450	2700	80	55W	50,000	Yes	★	Damp	Accent, 20° beam, White
			63026	LED10DP3/FL/TP	120	3	3.75	450	1240	2700	80	55W	25,000	Yes	★	Damp	Accent, 35° beam, Silver
		12	65135	LED12DP30S830/20	120	6	3.75	750	4600	3000	84	75W	25,000	Yes	★	Damp	Accent, 20° beam, Silver
			65136	LED12DP30S830/35	120	6	3.75	750	2050	3000	84	80W	25,000	Yes	★	Damp	Accent, 35° beam, Silver
			65137	LED12DP30S827/20	120	6	3.75	740	4400	2700	83	75W	25,000	Yes	★	Damp	Accent, 20° beam, Silver
			65138	LED12DP30S827/35	120	6	3.75	740	2000	2700	83	80W	25,000	Yes	★	Damp	Accent, 35° beam, Silver
			65133	LED12DP30S/FL/TP	120	3	3.75	740	2000	2700	83	80W	25,000	Yes	★	Damp	Accent, 35° beam, Silver
			65985	LED12DP30S827/25	120	6	3.75	740	3200	2700	83	75W	25,000	Yes	★	Damp	Accent, 25° beam, Silver
			65986	LED12DP30W827/25	120	6	3.75	740	3200	2700	83	75W	25,000	Yes	★	Damp	Accent, 25° beam, White
			65987	LED12DP30B827/25	120	6	3.75	740	3200	2700	83	75W	25,000	Yes	★	Damp	Accent, 25° beam, Black
			67256	LED12DP30S840/20	120	6	3.75	840	5300	4000	85	90W	25,000	Yes	★	Damp	Accent, 20° beam, Silver
			67257	LED12DP30S840/35	120	6	3.75	840	2200	4000	85	90W	25,000	Yes	★	Damp	Accent, 35° beam, Silver
Compact PAR30 Long Neck																	
	MED	10	75377	LED10P3L/NFL/TP	120	3	4.75	340	1400	3000	82	-	30,000	-		Damp	Accent, 24° beam, Silver
			61924	LED10DP3LS830/20	120	6	4.75	500	3720	3000	80	60W	50,000	Yes	★	Damp	Accent, 20° beam, Silver
			61925	LED10DP3LS827/20	120	6	4.75	450	3450	2700	80	55W	50,000	Yes	★	Damp	Accent, 20° beam, Silver
			68014	LED10DP3LS827/35	120	6	4.75	450	1240	2700	80	55W	25,000	Yes	★	Damp	Accent, 35° beam, Silver
			63027	LED10DP3L/FL/TP	120	3	4.75	450	1240	2700	80	55W	25,000	Yes	★	Damp	Accent, 35° beam, Silver
		12	65139	LED12DP3LS830/20	120	6	4.75	750	4600	3000	84	75W	25,000	Yes	★	Damp	Accent, 20° beam, Silver
			65140	LED12DP3LS830/35	120	6	4.75	750	2050	3000	84	80W	25,000	Yes	★	Damp	Accent, 35° beam, Silver
			65141	LED12DP3LS827/20	120	6	4.75	740	4400	2700	83	75W	25,000	Yes	★	Damp	Accent, 20° beam, Silver
			65142	LED12DP3LS827/35	120	6	4.75	740	2000	2700	83	80W	25,000	Yes	★	Damp	Accent, 35° beam, Silver
			65134	LED12DP3LS/FL/TP	120	3	4.75	740	2000	2700	83	90W	25,000	Yes	★	Damp	Accent, 35° beam, Silver

Information provided is subject to change without notice. Please verify all details with GE. All values are design or typical values when measured under laboratory conditions, and GE makes no warranty or guarantee, expressed or implied, that such performance will be obtained under end-use conditions.

* The life rating is based on the hours of operation the lamp will provide before reaching 70% of its original rating (L70)

** Minimum order quantity = 6

★ ENERGY STAR® status: Certified as meeting ENERGY STAR® guidelines.

UL 1993 Environmental Requirements for LED LAMPS

Location, damp - Exterior or interior location that is normally or periodically subject to condensation of moisture in, on, or adjacent to, electrical equipment, and includes partially protected locations.

Location, dry - Location not normally subject to dampness, may include a location subject to temporary dampness, i.e., building under construction, provided ventilation is adequate to prevent an accumulation of moisture.

Location, wet - Location in which water or other liquid can drip, splash, or flow on or against electrical equipment.

^ Incandescent or Halogen wattage equivalencies based on ENERGY STAR® guidelines using lumens or CBCP according to lamp type

Notes: 1) Product descriptions ending in /TP indicate a carded blister or clamshell package nestled in a tray for shelf display. Cards also designed for hook display.

2) LED A19 Locking device works on PC: 66390, 65385, 64128, 65386, 64130 and 64018

Get more information at
GELighting.com/ThinkLED