



Powering Business Worldwide

pe.eaton.com

Perfect Prox Photoelectric Sensor

13108AQD03

UPC:782113843629

Dimensions:

- Height: X
- Length: X
- Width: X

Notes: Sensor will detect a 90% reflectance card at the Sensing Range; sensor will ignore a 90% reflectance card at the Cutoff Range

Warranties:

- 3 year

Specifications:

- **Type:** Back Ground Suppression
- **Connection:** Dual key micro
- **Contact Rating:** 300 mA AC/DC at 20-264 Vac/15-30 Vdc
- **Contact Configuration:** AC: L1 switched, DC: NPN open collector
- **Enclosure Material:** Polyurethane Foam (RIM)
- **Environmental Rating:** NEMA 1, 3, 4, 4X, 6, 12, 13, IP69k
- **Input Voltage:** 20-264 Vac 50/60 Hz, 15-30 Vdc (NPN)
- **Led Indicators:** Output ON
- **Maximum Ac Current:** 300 mA
- **Number Of Pins:** 4 pin
- **Operating Temperature:** -40° to 158°F (-40° to 70°C)
- **Protection:** Latching S/C
- **Series:** Comet

Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)



- [Comet series - Photoelectric sensors](#)
- [Eaton Specification Sheet - 13108AQD03](#)

Certifications:

- cUL Recognized
- UL Recognized

Product compliance:

- CE Marked

© 2016 Eaton. All rights reserved.