



# 01116S

40A15 IF 130V (PK X 12)



**Application:** Offices, Schools, Restaurants, Medical, Retail, Hospitality, General Lighting

**Base:** Medium (E26)

**Coating:** PFA

**CRI:** 100

**Finish:** Inside Frost

**Lamp Type:** Incandescent

**Mean Design Lumens:** 405

**Package Weight:** 1.05 L

**Shape:** A15

**Type:** Incandescent

**Voltage:** 130 V

**Average Life Hours:** 1000

**Bulb:** A15

**Color Temperature:** 2850 K

**Diameter:** 1.25 IN

**Initial Lumens:** 405

**Length:** 3.50 IN

**Package (LxWxH):** 8.12 IN x 8.25 IN x 4.75 IN

**Pack By:** 12

**Special Features:** Shatter-Resistant

**UPC:** 726585011162

**Wattage:** 40.0 W

ULEPH,ROHS,NSF Splash Zone