



01116S

40A15 IF 130V (PK X 12)



Application: Offices, Schools, Restaurants, Medical, Retail, Hospitality, General Lighting

Base: Medium (E26)

Coating: PFA

CRI: 100

Dimmable: Yes

Initial Lumens: 405

Length: 3.50 IN

Package (LxWxH): 8.12 IN x 8.25 IN x 4.75 IN

Pack By: 12

Special Features: Shatter-Resistant

UPC: 726585011162

Wattage: 40.0 W

Average Life Hours: 1000

Bulb: A15

Color Temperature: 2850K

Diameter: 1.88 IN

Finish: Inside Frost

Lamp Type: Incandescent

Mean Design Lumens: 405

Package Weight: 1.05 L

Shape: A15

Type: Incandescent

Voltage: 130 V

ULEPH,ROHS,NSF Non-Food Zone,NSF Splash Zone