



01233

75A19 IF/RS/VS 120-130V (PK X 12)



Application: Rough & Vibration Service, General Lighting

Base: Medium (E26)

Coating: PFA

Diameter: 2.38 IN

Finish: Inside Frost

Lamp Type: Incandescent

Mean Design Lumens: 712

Package (LxWxH): 11.75 IN x 9.00 IN x 5.25 IN

Pack By: 12

Special Features: Shatter-Resistant

UPC: 726585012336

Wattage: 75.0 W

Average Life Hours: 1700

Bulb: A19

CRI: 100

Filament Type: RC-9

Initial Lumens: 712

Length: 3.94 IN

Operating Position: Universal

Package Weight: 1.60 L

Shape: A19

Type: Incandescent

Voltage: 120-130 V

ULEPH,ROHS,NSF Splash Zone



01233

75A19 IF/RS/VS 120-130V (PK X 12)



Application: Rough & Vibration Service, General Lighting

Base: Medium (E26)

Coating: PFA

Diameter: 2.38 IN

Finish: Inside Frost

Lamp Type: Incandescent

Mean Design Lumens: 712

Package (LxWxH): 11.75 IN x 9.00 IN x 5.25 IN

Pack By: 12

Special Features: Shatter-Resistant

UPC: 726585012336

Wattage: 75.0 W

Average Life Hours: 1700

Bulb: A19

CRI: 100

Filament Type: RC-9

Initial Lumens: 712

Length: 3.94 IN

Operating Position: Universal

Package Weight: 1.60 L

Shape: A19

Type: Incandescent

Voltage: 120-130 V

ULEPH,ROHS,NSF Splash Zone