



PRODUCT SPECIFICATION

COLEMAN PART NUMBER: 09724

DESCRIPTION: 16/2 w/gnd SPT-3 power supply cord with right angle attachment plug cap.

APPROVALS: UL Listed (UL 817)

CONSTRUCTION PARAMETERS:

Conductor:	16 AWG, 26/30 bunched bare copper
Conductor O.D. (nom):	0.063"
Insulated ground conductor O.D. (nom):	0.091"
Insulation material:	PVC, gray
Overall cable dimensions (nom):	0.181 x 0.413"
Attachment plug configuration:	NEMA 5-15P
Plug material:	PVC, gray
Open end configuration:	1.5" separation, 0.38" strip

ELECTRICAL PROPERTIES:

Temperature rating:	-20 to +60 °C
Maximum operating voltage:	125 VAC
Maximum operating current:	13 A
Maximum operating wattage:	1625 W

The information presented here is, to the best of our knowledge, true and accurate. However, since conditions of use are beyond our control, all recommendations or suggestions are presented without guarantee or responsibility on our part. We disclaim all liability in connection with the use of information contained herein or otherwise.

This specification is proprietary intellectual property of Coleman Cable Systems. Any information contained herein shall not be disclosed to any party without written consent of Coleman Cable Systems.

CUSTOMER APPROVAL: Approved by: _____ Date: _____
Title: _____