



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street
75964-7263, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



09726 6' Angle Appliance Cord

Coleman Cable

Catalog Number	09726
Manufacturer	Coleman Cable
Description	Portable Cord Set, Stranded, 26/30 MM Core Strands, #16 Awg Conductor Size, Copper Conductor Material, PVC Insulation Material, 13 A, Gray, 3 Conductors, 6 FT Overall Length, 0.059 In Outside Diameter, 0.48 LB/MFT
Weight per unit	0.4800 (lbs/ft)
Product Category	Portable Cord Sets

Features

Cord Type	SPT-3, -20 to 60 Deg C
Inlet	Male Plug 90 Degree
Length in meters	1.8288
Voltage Rating	125 V

Dimensions and Weight

Length	6 FT
--------	------

Descriptions

Additional Information	Conductor 26/30 Bare Copper Stranded; Conductor Outer Diameter 0.059 Inch; Insulation Material PVC
Commodity Description	Portable Cord Sets
Description	6' ANGLE APPLIANCE CORD

Manufacturer Information

Brand	Cables & Cords
GTIN	00029892097264
Model	9726
UPC	029892097264

Taxonomies, Classifications, and Categories

Category Description	CORD SETS [DRYER & RANGE CORDS & BOOSTER CABLES)
----------------------	--

Packaging

Carton	1
Package	25
Weight Per foot	0.48

Uses, Certifications, and Standards

Approval	UL mA
Configuration	NEMA 5-15P



PRODUCT SPECIFICATION

COLEMAN PART NUMBER: See table below
DESCRIPTION: 16/2 w/gnd SPT-3 replacement power supply cord
APPROVALS: UL Listed (UL 817)

CONSTRUCTION PARAMETERS:

Conductor: 16 AWG, 26/30 bunched bare copper
 Conductor O.D. (nom): 0.063"
 Insulated ground conductor O.D. (nom): 0.091"
 Insulation material: PVC, gray
 Overall cable dimensions (nom): 0.181 x 0.413"

Cord length: See table below
 Attachment plug configuration: NEMA 5-15P, see chart below
 Plug material: PVC, gray
 Open end configuration: 1.5" separation, 0.38" strip

ELECTRICAL PROPERTIES:

Temperature rating: -20 to +60 °C
 Nominal operating voltage: 125 VAC
 Maximum operating current: 13 A
 Maximum operating wattage: 1625 W

CATALOG NUMBERS

Catalog number	Cord length	Plug configuration
09724	4 ft	Right angle
09726	6 ft	
09733	3 ft	Straight
09734	4 ft	
09736	6 ft	

The information presented here is, to the best of our knowledge, true and accurate. However, since conditions of use are beyond our control, all recommendations or suggestions are presented without guarantee or responsibility on our part. We disclaim all liability in connection with the use of information contained herein or otherwise.

This specification is proprietary intellectual property of Coleman Cable Inc. Any information contained herein shall not be disclosed to any party without written consent of Coleman Cable Inc.

CUSTOMER APPROVAL: Approved by: _____ Date: _____
 Title: _____