

Catalog Number
Notes
Type

FEATURES & SPECIFICATIONS

INTENDED USE

Provides maintenance-free illumination for outdoor applications. Ideal illumination for walkways, yards, patios, play areas and driveways creating an inviting exterior space as well as providing safety and security.

CONSTRUCTION

Two tool-free adjustable heads allow for easy aiming up/down or side to side. Rugged cast aluminum, corrosion-resistant housing in bronze or white. Clear acrylic lenses are fully gasketed to keep out moisture, dirt and bugs.

Each head contains (3) 5000K* high performance LEDs which maintain 1,096 lumen output at 50,000 hour life. LED driver is 120V and operates at 60Hz.

Dusk-to-dawn photocell automatically turns light on at dusk and off at dawn for convenience and energy savings.

* Nominal correlated color temperature per ANSI C78-377-2008.

INSTALLATION

Wall or eave mount.

All mounting hardware included.

LISTINGS

UL/C-UL Certified to US and Canadian safety standards. Wet location listed.


WARRANTY

Five-year limited warranty. Full warranty terms located at

www.acuitybrands.com/CustomerResources/Terms_and_conditions.aspx.

Dimensions

All dimensions are inches (centimeters)



Outdoor General Purpose

Dusk-to-Dawn LED Floodlight 2 Adjustable Heads

High Performance LED



ORDERING INFORMATION

For shortest lead times, configure products using **bolded options**.

Example: OFLR 6LC 120 P BZ

OFLR	6LC	120	P	
Series	No. of Heads	Ballast/Voltage	Features	Finish
OFLR LED Floodlight	6LC 2 heads	120 120V residential electronic ballast	P Dusk-to-dawn photocell	BZ Bronze WH White

2-Head LED Floodlight with Photocell

PHOTOMETRICS

Full photometric data report available within 2 weeks from request. Consult factory.

