



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



OLVTCM CLNG MNT Led Vap Tite FXT

Lithonia Lighting - Acuity

Catalog Number	OLVTCM
Manufacturer	Lithonia Lighting - Acuity
Description	Energy-Efficient Solution For Environments Where Some Protection From Dust and Moisture and Larger Objects Is Required
Weight per unit	7.3 (lbs/each)
Product Category	Led Vapor Tight Lighting

Features

Ballast Type	Not Applicable
Lamp Included	Yes
Lamp Type	LED - Static
lumens	600 LM
Material	Aluminum
Number of Lamps	Not Applicable
pallet quantity	270
Socket Type	Not Applicable
Voltage Rating	MVOLT

Material, Color, and Finish

Color	Gray
color rendering index (cri)	74
color temperature	4000
fixture material	aluminum

Dimensions and Weight

Height	10.6250
Length	4.5600
Width	4.5600

Descriptions

Description	CLNG MNT LED VAP TITE FXT
extra long description	LITH OLVTCM M6 LED vapor tight ceil
Long Description	Energy-efficient solution for environments where some protection from dust and moisture and larger objects is required
Product Type	Surface Light
Special Features	Provides years of maintenance-free illumination for indoor or outdoor use in residential and commercial applications.



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Lithonia Lighting
GTIN	00753573237433
Manufacturers Part Number	OLVTCM M6
UPC	753573237433

Taxonomies, Classifications, and Categories

Category Description	LED HAZARDOUS LOCATION & VAPOR TIGHT LIGHTING
Type	AREA LIGHT

Packaging

Carton	1
Package	6
Weight	3.0000
Weight Per each	7.3099

Uses, Certifications, and Standards

Application	Warehouses
environmental conditions	OUTDOOR
standard	UL