



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2501 S. Fort Hood St.  
76542-2312, TX Killeen  
Phone: 254-554-5958  
Fax: 254-554-8423



## OLVTCM CLNG MNT Led Vap Tite FXT

*Lithonia Lighting - Acuity*

Catalog Number	OLVTCM
Manufacturer	Lithonia Lighting - Acuity
Description	Energy-Efficient Solution For Environments Where Some Protection From Dust and Moisture and Larger Objects Is Required
Weight per unit	7.3 (lbs/each)
Product Category	Led Vapor Tight Lighting

### Features

Ballast Type	Not Applicable
Lamp Included	Yes
Lamp Type	LED - Static
lumens	600 LM
Material	Aluminum
Number of Lamps	Not Applicable
pallet quantity	270
Socket Type	Not Applicable
Voltage Rating	MVOLT

### Material, Color, and Finish

Color	Gray
color rendering index (cri)	74
color temperature	4000
fixture material	aluminum

### Dimensions and Weight

Height	10.6250
Length	4.5600
Width	4.5600

### Descriptions

Description	CLNG MNT LED VAP TITE FXT
extra long description	LITH OLVTCM M6 LED vapor tight ceil
Long Description	Energy-efficient solution for environments where some protection from dust and moisture and larger objects is required
Product Type	Surface Light
Special Features	Provides years of maintenance-free illumination for indoor or outdoor use in residential and commercial applications.



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2501 S. Fort Hood St.  
76542-2312, TX Killeen  
Phone: 254-554-5958  
Fax: 254-554-8423

## Manufacturer Information

Brand	Lithonia Lighting
GTIN	00753573237433
Manufacturers Part Number	OLVTCM M6
UPC	753573237433

## Taxonomies, Classifications, and Categories

Category Description	LED HAZARDOUS LOCATION & VAPOR TIGHT LIGHTING
Type	AREA LIGHT

## Packaging

Carton	1
Package	6
Weight	3.0000
Weight Per each	7.3099

## Uses, Certifications, and Standards

Application	Warehouses
environmental conditions	OUTDOOR
standard	UL