



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

149 North Wilson St.
76028-0000, TX Burleson
Phone: 817-447-0192
Fax: 817-426-1193



OLVTWMM6 Wall MNT Vap Tite FXT

Lithonia Lighting - Acuity

Catalog Number	OLVTWMM6
Manufacturer	Lithonia Lighting - Acuity
Description	Energy-Efficient Solution For Environments Where Some Protection From Dust and Moisture and Larger Objects Is Required
Weight per unit	2.9 (lbs/each)
Product Category	Led Vapor Tight Lighting

Features

Ballast Type	Not Applicable
Hardware	Yes
Lamp Included	Yes
Lamp Type	LED - Static
lumens	600 LM
Material	Aluminum
Number of Lamps	Not Applicable
pallet quantity	144
Power Source	Hardwired
Shape	OVAL
Socket Type	Not Applicable
Voltage Rating	MVOLT
Warranty	5
Wattage	15

Material, Color, and Finish

Color	Gray
color rendering index (cri)	74
color temperature	4000
fixture material	aluminum
Lens Material	Glass
Style	Traditional

Dimensions and Weight

Height	11.25
Length	7.375
Width	4.625



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

149 North Wilson St.
76028-0000, TX Burleson
Phone: 817-447-0192
Fax: 817-426-1193

Descriptions

Description	WALL MNT VAP TITE FXT
extra long description	LITH OLVTWM M6 LED vapor tight wall
Long Description	Energy-efficient solution for environments where some protection from dust and moisture and larger objects is required
Product Type	Wallpack
Special Features	Provides years of maintenance-free illumination for indoor or outdoor use in residential and commercial applications.

Manufacturer Information

Brand	Lithonia Lighting
GTIN	00753573237457
Manufacturers Part Number	OLVTWM M6
UPC	753573237457

Taxonomies, Classifications, and Categories

Category Description	LED HAZARDOUS LOCATION & VAPOR TIGHT LIGHTING
Type	AREA LIGHT

Packaging

Carton	1
Weight	3.5
Weight Per each	2.9

Uses, Certifications, and Standards

Application	Warehouses
environmental conditions	OUTDOOR
Mounting	SURFACE
standard	UL