

Specifications



Eaton OS310U-W

Eaton occupancy sensor switch, Motion sensor with nightlight, Flush, 120V, Wire leads, Maintained closure, White, Incand, MLV, ELV, Flrsnt, CFL, LED, halo, 1-pole, 3-way, 1-phase, 1000 sq ft, Occupancy, 1000W 710872

General specifications

PRODUCT NAME	Eaton occupancy sensor switch
CATALOG NUMBER	OS310U-W
UPC	032664710872
PRODUCT LENGTH/DEPTH	3.31 in
PRODUCT HEIGHT	5.44 in
PRODUCT WIDTH	2.88 in
PRODUCT WEIGHT	0.001 lb
CERTIFICATIONS	NOM cULus Listed
PRODUCT TYPE	Occupancy sensor switch



Powering Business Worldwide

Product specifications

SPECIAL FEATURES	Motion sensor with nightlight
TYPE	Occupancy sensor switch
VOLTAGE RATING	120 V
NUMBER OF POLES	Single-pole
PHASE	Single-phase
POWER CONSUMPTION	1000 W
WIRING METHOD	Wire leads
SENSOR TYPE	Occupancy
MOUNTING METHOD	Flush
CLOSURE TYPE	Maintained
LOAD TYPE	ELV CFL LED MLV INC FLR HAL
NUMBER OF WAYS	Three-way
RANGE	1000 sq ft
COLOR	White

Resources

SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - OS310U-W
	Motion sensor switch with nightlight spec sheet

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

