



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Eaton's Meter Socket

1005826ACH

UPC:786685160221

### Dimensions:

- **Height:** 10.88 IN
- **Length:** 3.5 IN
- **Width:** 8 IN

**Weight:**5 LB

### Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Specifications:

- **Type:** Residential type cover
- **Amperage Rating:** 125A
- **Feed Type:** Underground
- **Hub Type:** Solid Top
- **Line:** #8-2/0 AWG
- **Number Of Jaws:** Four-jaw
- **Phase:** Single-phase
- **Bypass:** Horn bypass
- **Number Of Sockets:** 1
- **Number Of Wires:** Three-wire
- **Security:** Ringless
- **Voltage Rating:** 600V

### Supporting documents:

- [Eaton's Volume 1-Residential and Light Commercial](#)
- [Single Meter Sockets](#)
- [Eaton Specification Sheet - 1005826ACH](#)
- [Dimensional Drawing - 10006486 SKT 125A 1P ST-H7112A](#)

### Certifications:



- UL Listed

**Product compliance:** No Data

---

© 2016 Eaton. All rights reserved.