# Eaton 1005826ACH

# Catalog Number: 1005826ACH

Eaton meter socket, Resi type cover, 125A, Under, Solid top, #8-2/0 AWG, 4-jaw, 1-ph, #8-2/0 AWG, Horn bypass, 3-wire, Ringless, 600 Vac

### General specifications



Eaton meter socket

UPC

786685160221

**Product Height** 

10.87 in

**Product Weight** 

5 lb

Catalog Number

1005826ACH

Product Length/Depth

3.5 in

Product Width

8 in

Warranty

Eaton Selling Policy 25-000, one (1) year

from the date of installation of the

Product or eighteen (18) months from the

date of shipment of the Product,

whichever occurs first.



**UL** Listed



## defaultTaxonomyAttributeLabel

# Type Residential type cover Amperage Rating 125A Feed type Bottom Number of jaws Four-jaw Phase Single-phase Utility approvals TX: City Public Service of San Antonio (CPSB)

#8-2/0 AWG

Load

Line

#8-2/0 AWG

Number of wires

Three-wire

Hub type

Solid top

Security

Ringless

Voltage rating

600 V

Bypass

Horn

Number of sockets

1

### Resources

### **Brochures**

Single Meter Sockets

### Catalogs

Eaton's Volume 1—Residential and Light Commercial

### Drawings

Dimensional Drawing - 10006486 SKT 125A 1P ST-H7112A

### Specifications and datasheets

Eaton Specification Sheet - 1005826ACH



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

Reserved.

Eaton is a registered trademark.

All other trademarks are © 2024 Eaton. All Rights property of their respective owners.



Eaton.com/socialmedia