

17986 - 100PAR/H/FL25

GE energy-efficient halogen 100 watt PAR38 floodlight 1-pack

- GE energy-efficient halogen bulbs deliver crisp, white light. This unsurpassed light quality is ideal for adding depth, drama and interest to any outdoor space. These GE energy-efficient halogen floodlights use less energy than standard halogen bulbs, saving money on energy. GE energy-efficient halogen floodlights feature lenses designed to provide a precise beam pattern, dispensing broad beams of crisp, white light on your home's exterior and andscaping. Designed with a unique all-weather construction, they withstand harsh weather conditions better than regular bulbs. Use these bulbs in outdoor stake light and security fixtures and create a dramatic effect
- Designed with a unique all-weather construction, they withstand harsh weather conditions better than regular hulbs
- Uses Halogen technology for a brighter, crisper light
- GE's Floodlights cast a wider beam that adds drama to driveways and yards.
- Estimated yearly energy costs \$12.05 based on 3 hours per day \$0.11 per kWh
- Lasts 1.8 years based on 3 hours per day usage
- PAR38 outdoor floodlight with medium base for use in security and wet rated fixtures

Energy Savings DIA. MOL









CAUTIONS & WARNINGS

Caution

- Lamp may shatter and cause injury if broken
- Do not use lamp if outer glass is scratched or broken.

Warning

- Risk of Burn
- Allow lamp to cool before handling.
- Pressurized lamp--unexpected rupture may cause injury, fire, or property damage
- Do not use lamp if outer glass is scratched or broken.
- Risk of Fire
- Keep combustible materials away from lamp.
- Risk of Electric Shock
- Turn power off before inspection, installation or removal.

GENERAL CHARACTERISTICS

Lamp Type Halogen - PAR

Bulb PAR38

Base Medium Skirt (E26/50x39)

Filament CC-8 Rated Life 2000.0 hrs

Primary Application Yard Stake;Indoor and outdoor Floodlight

PHOTOMETRIC CHARACTERISTICS

Initial Lumens 1500.0 Center Beam Candlepower 5000.0

(CBCP)

Color Temperature 2900.0 K Beam Spread 25.0 ° Nominal Initial Lumens per Watt 15

ELECTRICAL CHARACTERISTICS

Wattage 100.0 Voltage 120.0

DIMENSIONS

Maximum Overall Length 5.3130 in(135.0 mm)

(MOL)

Bulb Diameter (DIA) 4.750 in(120.6 mm)

PRODUCT INFORMATION

Product Code 17986

Description 100PAR/H/FL25

Standard Package Case

Standard Package GTIN 10043168179864

Standard Package Quantity 6
Sales Unit Unit
No Of Items Per Sales Unit 1
No Of Items Per Standard 6

Package

UPC 043168179867