



CAT #	A	B	C
1094	3.50	1.625	2.00
1096	3.50	2.3125	2.1875



CAT #	A	B	C	D
1011	1.0625	1.50	.625	.875
1012	1.3125	1.5625	.625	1.062
1013	1.625	2.00	1.00	1.3125
1014	2.00	2.125	1.00	1.6875
1015	2.25	2.375	1.125	1.9375
1016	2.6875	2.4375	1.25	2.375
1017	3.25	3.50	1.75	2.875
1018	4.00	3.875	1.8125	3.50
1019	4.125	4.00	1.9375	4.00
1020	5.00	4.1875	2.00	4.50
1020A	6.125	5.375	2.50	5.625
1020B	7.25	6.375	3.00	6.625



CAT #	A	B	C
1021	1.00	1.4375	.6875
1022	1.25	1.625	.6875
1023	1.5625	1.875	.8750
1024	2.00	1.9375	.9375
1025	2.25	2.125	.9375
1026	2.6875	2.125	.9375
1027	3.3125	3.00	1.3125
1028	4.00	3.0625	1.25
1029	4.50	3.00	1.1875
1030	5.00	3.25	1.375
1030A	7.25	4.375	1.625
1030B	9.3125	7.00	2.25

METER OFFSET

TOPAZ CAT #	UPC#	SIZE	UNIT CTN	SHIP CASE	WT/ CASE	PVC
1094	23116	1 1/4"	—	15	8	
1096	23117	2"	—	8	24	



COUPLINGS

TOPAZ CAT #	UPC#	SIZE	UNIT CTN	SHIP CASE	WT/ CASE
1011	23001	1/2"	—	200	4
1012	23002	3/4"	—	125	5
1013	23003	1"	—	70	6
1014	23004	1 1/4"	—	40	7
1015	23005	1 1/2"	—	30	10
1016	23006	2"	—	40	14
1017	23007	2 1/2"	—	20	35
1018	23008	3"	—	40	50
1019	23009	3 1/2"	—	30	70
1020	23401	4"	—	20	90
1020A	23011	5"	—	10	140
1020B	23012	6"	—	8	185



FEMALE ADAPTERS

TOPAZ CAT #	UPC#	SIZE	UNIT CTN	SHIP CASE	WT/ CASE
1021	23013	1/2"	—	200	3
1022	23014	3/4"	—	125	4
1023	23015	1"	—	70	5
1024	23016	1 1/4"	—	40	10
1025	23017	1 1/2"	—	30	11
1026	23018	2"	—	40	15
1027	23019	2 1/2"	—	20	40
1028	23402	3"	—	40	47
1029	23021	3 1/2"	—	30	65
1030	23022	4"	—	20	85
1030A	23023	5"	—	10	140
1030B	23024	6"	—	8	185

