



Long Nose Multi-Purpose Wire Stripper



Klein Tools Cat. No. 1025 Long Nose Wire Stripper combines multiple electrician tools into one professional-grade instrument. This wire stripper tool features precision cutting for 10-20 AWG solid and 12-22 AWG stranded wire, plus crimping pliers functionality for terminals and connectors. Heavy duty wire cutters with ergonomic grips provide superior control, while the narrow long nose design accesses tight spaces while screw shearing capability handles 4-40 to 10-24 screws.

Specifications

Type:	Multi Tool; Wire Stripper	Application:	10 - 20 AWG Solid, 12 - 22 AWG Stranded
Special Features:	Crimps, Shears, Strips Wires	Ratcheting:	No
Material:	Steel	Finish:	Black Oxide
Strips and Cuts:	10-20 AWG Solid; 12-22 AWG Stranded	Screw Shearing:	4-40; 5-40; 6-32; 8-32; 10-32; 10-25
Jaw Capacity:	1.19" (3 cm)	Jaw Length:	2" (5.1 cm)
Jaw Width:	0.125" (0.3 cm)	Jaw Thickness:	0.38" (11 cm)
Crimping Capacity:	10-22 AWG Insulated, Non-Insulated Terminals, 7-8 mm Ignition Terminals	Blade Material:	Steel
Cutting Length:	0.504" (1.3 cm)	Overall Length:	8.25" (21 cm)
Overall Height:	0.62" (1.6 cm)	Overall Width:	2.52" (6.4 cm)
Handle Type:	Molded	Handle Material:	TPE
Handle Color:	Blue; Black	Handle Finish:	Plastic
Handle Length:	4.51" (11.5 cm)	Locking Handle:	No
Insulated:	No	Weight:	7.8 oz (220.9 g)