

Eaton 10250H2740

Catalog Number: 10250H2740

Eaton 10250T pushbutton, 10250H, Assembled control station, 30.5 mm, Heavy-Duty, NEMA 3, 3R, 4, 4X, 13, Mechanically interlocked, Die cast, FOR/REV, Horizontal/vertical, Two element



General specifications

Product Name

Eaton 10250T pushbutton

Catalog Number

10250H2740

UPC

782113223070

Product Length/Depth

7.9 in

Product Height

5 in

Product Width

4 in

Product Weight

1.8 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Compliances

CE Marked

Certifications

UL 505

CSA Certified

Catalog Notes

No legend on button. Specify any Standard legend, no price change. Open type enclosure. Round button.

defaultTaxonomyAttributeLabel

Type

30.5 mm, Heavy-Duty

Enclosure

NEMA 4
NEMA 3R
NEMA 4X
NEMA 3
NEMA 13

Actuator

Mechanically interlocked

Enclosure material

Die cast

Legend

FOR REV

Illumination

PresTest

Series

10250H

Product category

Assembled control station

Number of elements

2

Mounting method

Vertical
Horizontal

Degree of protection

NEMA 3R
NEMA 13
NEMA 12
NEMA 4
NEMA 3

Resources

Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

Multimedia

How to size and select a Power Supply

Specifications and datasheets

Eaton Specification Sheet - 10250H2740

Warranty guides

Selling Policy 25-000 - Distribution and Control Products and Services



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)