# Eaton 10250H364

## Catalog Number: 10250H364

Eaton 10250T pushbutton,10250H, Assembled control station, 30.5 mm, Heavy-Duty, NEMA 3, 3R, 4, 4X, 13, Flush, Polyester, START/STOP, Horizontal/vertical, Two element

## General specifications



Eaton 10250T pushbutton

UPC

782113203157

**Product Height** 

4.5 in

**Product Weight** 

1.9 lb

Catalog Number

10250H364

Product Length/Depth

7.75 in

**Product Width** 

4.5 in

Warranty

Eaton Selling Policy 25-000, one (1) year

from the date of installation of the

Product or eighteen (18) months from the

date of shipment of the Product,

whichever occurs first.

Compliances

CE Marked

Certifications

CSA Certified

UL 505

Catalog Notes
Chrome Bezel



## default Taxonomy Attribute Label

#### Type

30.5 mm, Heavy-Duty

#### Enclosure

NEMA 3

NEMA 13

NEMA 4X

NEMA 3R

NEMA 4

#### Actuator

Flush

## Enclosure material

Polyester

#### Legend

START STOP

#### Illumination

PresTest

#### Series

10250H

## **Product category**

Assembled control station

#### Number of elements

2

## Mounting method

Vertical

Horizontal

## Degree of protection

NEMA 12

NEMA 13

NEMA 3

NEMA 3R

NEMA 4

## Resources

#### Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

#### Multimedia

How to size and select a Power Supply

#### Specifications and datasheets

Eaton Specification Sheet - 10250H364

## Warranty guides

Selling Policy 25-000 - Distribution and Control Products and Services



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

Reserved.

Eaton is a registered trademark.

All other trademarks are © 2024 Eaton. All Rights property of their respective owners.



Eaton.com/socialmedia