



Powering Business Worldwide

pe.eaton.com

30.5 mm, Heavy-Duty Selector Switch Operator

10250T1311

UPC:782113219691

Dimensions:

- **Height:** 2.2 IN
- **Length:** 1.9 IN
- **Width:** 1.9 IN

Weight: .25 LB

Warranties:

- 1 year

Specifications:

- **Type:** 30.5 mm, Heavy-Duty
- **Actuator:** Knob
- **Actuator Color:** Black
- **Cam Code:** Cam 1
- **Illumination:** Non-illuminated
- **Number Of Positions:** Two-position
- **Product Category:** Selector switch
- **Rating:** NEMA 3, 3R, 4, 4X, 12, 13
- **Series:** 10250T
- **Throw Type:** 60°

Supporting documents:

- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [Eaton Specification Sheet - 10250T1311](#)

Certifications:

- CSA Certified
- UL Listed

Product compliance:

- CE Marked





Powering Business Worldwide

pe.eaton.com

30.5 mm, Heavy-Duty Selector Switch Operator

10250T1311

UPC:782113219691

Dimensions:

- **Height:** 2.2 IN
- **Length:** 1.9 IN
- **Width:** 1.9 IN

Weight: .25 LB

Warranties:

- 1 year

Specifications:

- **Type:** 30.5 mm, Heavy-Duty
- **Actuator:** Knob
- **Actuator Color:** Black
- **Cam Code:** Cam 1
- **Illumination:** Non-illuminated
- **Number Of Positions:** Two-position
- **Product Category:** Selector switch
- **Rating:** NEMA 3, 3R, 4, 4X, 12, 13
- **Series:** 10250T
- **Throw Type:** 60°

Supporting documents:

- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [Eaton Specification Sheet - 10250T1311](#)

Certifications:

- CSA Certified
- UL Listed

Product compliance:

- CE Marked



