

# Eaton 10250T197HLRP2A

Catalog Number: 10250T197HLRP2A

Eaton 10250T pushbutton, Class I Division 2 Indicating Light, Watertight and Oiltight, Standard actuator, LED, Full voltage, NEMA 3, 3R, 3S, 4, 4X, 12, 13, NEC Class I Division 2, Groups B, C and D, Red, Plastic, 120 V

## General specifications



### Product Name

Eaton 10250T pushbutton

### UPC

782114541319

### Product Height

0.01 in

### Product Weight

0.01 lb

### Compliances

CE Marked

### Catalog Number

10250T197HLRP2A

### Product Length/Depth

0.01 in

### Product Width

0.01 in

### Warranty

1 year

### Certifications

CSA Certified

UL Listed



Powering Business Worldwide

## defaultTaxonomyAttributeLabel

### Type

30.5 mm, Class I Division 2 Watertight/Oiltight

### Light unit type

LED, full voltage

### Lens material

Plastic

### Light unit voltage

24 Vac/dc

### Series

10250T

### Actuator

Standard

### Lens color

Red

### Rating

NEMA 4X

NEC Class I Division 2, Groups B, C and D

NEMA 13

NEMA 3R

NEMA 12

NEMA 4

NEMA 3

NEMA 3S

## Resources

### Catalogs

[Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions](#)

### Multimedia

[How to size and select a Power Supply](#)

### Specifications and datasheets

[Eaton Specification Sheet - 10250T197HLRP2A](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)