

Eaton 10250T21KB-POP

Catalog Number: 10250T21KB-POP

Eaton Heavy-duty assembled selector switch, 10250T, 30.5 mm, 60° throw, NEMA 3, 3R, 4, 4X, 12, 13, Non-illuminated, Three-position, Maintained, Knob, Black actuator, 2NO



General specifications

Product Name	Catalog Number
Eaton 10250T pushbutton	10250T21KB-POP
UPC	Product Length/Depth
786685393902	5.6 in
Product Height	Product Width
5.9 in	2.8 in
Product Weight	Warranty
0.4 lb	1 year
Compliances	Certifications
CE Marked	CSA Certified
	UL Listed

Type

30.5 mm, Heavy-Duty

Actuator color

Black

Actuator

Knob

Illumination

Non-illuminated

Number of positions

3

Operating mode

Maintained

Rating

NEMA 3, NEMA 3R, NEMA 4, NEMA 4X, NEMA 12, NEMA 13

Series

10250T

Throw type

60 °

Contact configuration

2 NO

Catalogs

[Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions](#)

Multimedia

[How to size and select a Power Supply](#)

Specifications and datasheets

[Eaton Specification Sheet - 10250T21KB-POP](#)

[Quick Selector - 10250T Pilot Devices](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)