



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



10250T330 Pot KNB and Dial Plate *Eaton Corp*

| | |
|------------------|---|
| Catalog Number | 10250T330 |
| Manufacturer | Eaton Corp |
| Description | Eaton 10250T Potentiometer, Operator Only, 30.5 MM, Heavy-Duty, 2W DC Coil Power, Nema 3, 3R, 4, 4X, 12, 13 |
| Weight per unit | 0.2500 (lbs/each) |
| Product Category | Push Button Components |

Features

| | |
|------------|-----------------------------------|
| dimensions | 3.5000 IN X 2.4000 IN X 2.1000 IN |
| media | Yes |

Descriptions

| | |
|------------------------|---|
| Description | POT KNB AND DIAL PLATE |
| extra long description | ETN 10250T330 POT KNB AND DIAL PLAT |
| Features | Eaton's 10250T line of 30.5 mm pushbuttons features a heavy-duty zinc die cast construction. Reliability nibs improve contact reliability even under dry circuit and fine dust conditions. In addition, drainage holes prevent the buildup of liquid inside the operator, which can prevent operation in freezing environments. |
| Long Description | Eaton 10250T Potentiometer, operator only, 30.5 mm, Heavy-Duty, 2W DC coil power, NEMA 3, 3R, 4, 4X, 12, 13 |
| Product Type | Pot KNB and Dial Plate |
| Special Features | 2W DC coil power |

Manufacturer Information

| | |
|---------------------------|---------------------|
| Brand | EATON CUTLER-HAMMER |
| GTIN | 00782113225784 |
| Manufacturers Part Number | 10250T330 |
| UPC | 782113225784 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-------------------------|
| Category Description | OILTIGHT OPERATORS.30MM |
| Type | Potentiometer |

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Package | 10 |
| Weight Per each | 0.25 |

Uses, Certifications, and Standards

| | |
|-------------|--|
| Application | Ind Facilities & Factories - Facility: Automation and Monitoring |
| standard | CSA Certified,UL Listed,CE Marked |