

Eaton 10250T397L

Catalog Number: 10250T397L

Eaton 10250T pushbutton, 30.5 mm, Heavy-Duty, 40 mm, NEMA 3, 3R, 4, 4X, 12, 13, Illuminated, Momentary, LED, full voltage (without lamp) light unit, Flush, Chrome bezel, Bayonet base

General specifications



Product Name

Eaton 10250T pushbutton

Catalog Number

10250T397L

UPC

782114753651

Product Length/Depth

1.63 in

Product Height

2.25 in

Product Width

1.59 in

Product Weight

0.01 lb

Warranty

1 year

Compliances

CE Marked

Certifications

UL Listed

CSA Certified

Catalog Notes

Unit does not include lamp. Order LED separately to match lens.

defaultTaxonomyAttributeLabel

Special features

10250T series

Type

30.5 mm Heavy-Duty Watertight/Oiltight

Bezel

Chrome

Operating mode

Momentary

Illumination

Illuminated

Series

10250T

LED lamp number

Bayonet base

Light unit type

LED, full voltage (without lamp)

Mounting method

Flush

Rating

NEMA 13

NEMA 4X

NEMA 4

NEMA 12

NEMA 3

NEMA 3R

Size

40 mm

Resources

Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

Multimedia

How to size and select a Power Supply

Specifications and datasheets

Eaton Specification Sheet - 10250T397L



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)