



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street
75964-7263, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



10250T411 120V, No Lense, Illuminated Pushbutton

Eaton Corp

Catalog Number	10250T411
Manufacturer	Eaton Corp
Description	Illuminated Pushbutton, 10250T Series, Momentary Switch Action, Illuminated, 2.4 X 2.1 X 3.4 In Size, 0.35 LB
Weight per unit	0.3500 (lbs/each)
Product Category	Push Button Components

Features

bezel	Chrome
dimensions	60.9600millimetreX53.3400millimetreX86.3600millimetre
illumination	Illuminated
light unit type	Incandescent, transformer
light unit voltage	120 Vac
Operating Mode	Momentary
Rating	NEMA 3, 3R, 4, 4X, 12, 13

Descriptions

Description	120V,NO LENSE,ILLUMINATED PUSHBUTTON
-------------	--------------------------------------

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782113203713
UPC	782113203713

Taxonomies, Classifications, and Categories

Category Description	OILTIGHT OPERATORS.30MM
igcc	5210
Type	30.5 mm, Heavy-Duty
unspsc code	39122216

Packaging

Carton	1
Weight Per each	0.35

Uses, Certifications, and Standards

Mounting	FLUSH
standard	UL Listed;CSA Certified;CE Marked



Powering Business Worldwide

pe.eaton.com

30.5 mm, Heavy-Duty Pushbutton Operator

10250T411

UPC:782113203713

Dimensions:

- **Height:** 3.4 IN
- **Length:** 2.4 IN
- **Width:** 2.1 IN

Weight: .35 LB

Warranties:

- 1 year

Specifications:

- **Type:** 30.5 mm, Heavy-Duty
- **Bezel:** Chrome
- **Illumination:** Illuminated
- **Led Lamp Number:** #755
- **Light Unit Type:** Incandescent, transformer
- **Light Unit Voltage:** 120 Vac
- **Mounting:** Flush
- **Operating Mode:** Momentary
- **Rating:** NEMA 3, 3R, 4, 4X, 12, 13
- **Series:** 10250T

Supporting documents:

- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [Eaton Specification Sheet - 10250T411](#)

Certifications:

- CSA Certified
- UL Listed

Product compliance:

- CE Marked



