



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



10316H1600 1NO 1NC 10A TD Limit Switch

Eaton Corp

Catalog Number	10316H1600
Manufacturer	Eaton Corp
Description	Eaton 10316 Hazardous Location Limit Switch, Type LP Pneumatic Time Delay Limit Switch, Pneumatic Time Delay, Die Cast Zinc Enclosure, 10A Max Ac, 0.2A Max DC, 1NO-1NC, 10A At 120VAC / 0.2A At 120VDC, Screw Terminals, Side Rotary
Weight per unit	1.9 (lbs/each)
Product Category	Severe Duty Limit Switches

Features

connection	Screw Terminal
Contact Configuration	1 NO-1 NC
Contact Rating	10A at 120Vac / 0.2A at 120Vdc

Descriptions

Description	1NO 1NC 10A TD LIMIT SWITCH
extra long description	ETN 10316H1600 Type LP Pneumatic Ti
Features	Type LX, CX and CBX limit switches are designed for extreme environmental service in NEMA 7 9 locations where the danger of an internal or external explosion of flammable gases, vapors, metal alloy or grain dust exists. Type CB provides excellent corrosion-resistant properties in NEMA 4X applications. Markets served include mining, grain storage, forest products, petrochemical, pharmaceutical and waste and sewage management.
Long Description	Eaton 10316 hazardous location limit switch, Type LP Pneumatic Time Delay Limit Switch, Pneumatic Time Delay, Die Cast Zinc enclosure, 10A max AC, 0.2A max DC, 1NO-1NC, 10A at 120Vac / 0.2A at 120Vdc, Screw Terminals, Side Rotary
Product Type	Type LP Pneumatic Time Delay Limit Switch

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782113266336
Manufacturers Part Number	10316H1600
UPC	782113266336

Taxonomies, Classifications, and Categories

Category Description	LIMIT SWITCHES
Type	Hazardous location limit switch



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	1.85

Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels and OEMs
Operating Temperature	32
standard	UL Listed,Contact Manufacturer