

Lampholders

Lampholder adapters & accessories

Product description

Keyless switch Medium base 660W, 250V/AC

Design features

• One piece screwshell with porcelain base







Rati W	ing V/AC	Description	Color	Catalog no.	(RoHS)
660	250	Phenolic medium base socket, extends 1.38" (34.9mm)	BK	□1054	•

Listed to UL496, file no. E15055; CSA certified to C22.2, no. 43; NOM certified

469



Design features

Product description

• 1.50" (38.1mm) clamp fits ceiling lampholders, sign and scoreboard Attachon lampholders

Lampholder adapters & accessories

- 1465 is high-strength impact-resistant thermoplastic
- Easy-open guard permits relamping without removing guard

Lamp guards

Description	Color	Catalog no.	_
Metal lamp guard with 1.50" (38.1mm) collar, 100W bulb max.	Steel	□ 469B	
Plastic lamp guard with adjustable collar, 200W max.	Υ	□ 1465Y	•

Color ordering information:

BK (Black), Steel, Y (Yellow)



Dimensional information: B-73 Specification information: Please visit www.eaton.com/wiringdevices Compliances, specifications and availability are subject to change without notice.



Indicates NAFTA compliant - Page G-21



RoHS compliant - Page G-21