

# Eaton 1086-4CHC

Catalog Number: 1086-4CHC

Eaton B-Line series JIC panel enclosure, 10" height, 6" length, 8" width, NEMA 4, Hinged cover, 4CHC enclosure, Wall mount, Small single door, External mounting feet, Carbon steel, Seamless poured in-place gasket

## General specifications



Photo is representative

|   |                      |
|---|----------------------|
| Product Name                            | Catalog Number       |
| Eaton B-Line series JIC panel enclosure | 1086-4CHC            |
| UPC                                     | Product Length/Depth |
| 782051701746                            | 6 in                 |
| Product Height                          | Product Width        |
| 10 in                                   | 8 in                 |
| Product Weight                          | Certifications       |
| 7.8 lb                                  | UL 50                |
|   | CSA C22.2.           |
|   | NEMA                 |

## Material/finish

### Material

Carbon steel

### Wall thickness

16 gauge

### Finish color

Painted

### Color

ANSI 61 gray

## Model

### Style

Small single door

### Model

4CHC enclosure

### Cover type

Hinged

### Mounting method

Wall

### Mounting hole details

External mounting feet

### Closure type

Hinged

### Special features

Continuous piano hinge with s.s. pin & door clamp

## Standards

### NEMA Rating

4

### Country of origin

US

## Resources

### Catalogs

[Electrical Enclosure Catalog](#)

### Specifications and datasheets

[Eaton Specification Sheet - 1086-4CHC](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)