



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



10T3QCL12V 10W Hal T3 Bipin 30K *Sylvania-Ledvance*

Catalog Number	10T3QCL12V
Manufacturer	Sylvania-Ledvance
Description	OBS58658 Tungsten Halogen Quartz Bi Pin Standard Low Pressure Clear Finish Uv Stop With Transverse Filament G4 Bi Pin Base 10WATT 12VOLT 2000HR Lamp Life
Weight per unit	0.0100 (lbs/each)
Product Category	Halogen Decorative B, F, G, T,

Features

average life	2000
Base	G4 Bipin
dimnable	Yes
lumens	140
Shape	T3
start type	Instant
Voltage Rating	12
Wattage	10

Material, Color, and Finish

color rendering index (cri)	100
color temperature	3000
Finish	Clear

Descriptions

Description	10W HAL T3 BIPIN 30K
extra long description	SYL 10T3Q/CL-12V/58658 10T3QCL 12V
Long Description	OBS58658 Tungsten Halogen Quartz Bi Pin STANDARD Low Pressure Clear Finish UV Stop With Transverse Filament G4 Bi Pin Base 10Watt 12Volt 2000Hr Lamp Life
Product Type	10T3QCL 12V 40/CS 1/Sku

Manufacturer Information

Brand	Sylvania (Usc)
GTIN	00046135586583
Manufacturers Part Number	10T3Q/CL-12V/58658
sub brand	STANDARD Bi-Pin
UPC	046135586583



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	QUARTZ
Type	HALOGEN

Packaging

Carton	1
Package	40
Weight Per each	0.01

Uses, Certifications, and Standards

Application	Medium Screwbase or bi-pin
-------------	----------------------------