



Job Name:

Job Type:

Comments:

Quantity:

11037AT-15: 6" Regressed Eyeball Trim

Dimensions:

Diameter: 7 3/8"

Height: 4 1/8"

Material List:

1 Trim - Steel - White

1 Body - Steel - White

Safety Listing:

C-UL-US Listed for Damp Locations



Collection: Recessed Trims

R30 Regressed Eyeball Trim with Metal Baffle in White Finish

IC Airtight High Wattage: PAR-30L 75w, BR-30 65w, Non-IC:
 PAR-30L 75w, BR-30 65w, IC Airtight: PAR-30L 75w, BR-30 65w, IC
 Airtight Shallow: PAR-30L 75w, BR-30 65w

UPC #:785652110375

Finish: White (15)

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Frt. Class	UPS Ship
Individual	11037AT-15	1	785652110375	7.5	7.5	4.5	0.146	1.3	100	Yes
Master Pack		12	10785652110372	27	16	9	2.25	17.2	100	Yes
NJ Pallet		288		48	40	69	76.667	412.8		No
NV Pallet		288		48	40	69	76.667	412.8		No



Job Name:

Job Type:

Comments:

Quantity:

11037AT-15: 6" Regressed Eyeball Trim

Dimensions:

Diameter: 7 3/8"

Height: 4 1/8"

Material List:

1 Trim - Steel - White

1 Body - Steel - White

Safety Listing:

C-UL-US Listed for Damp Locations



Collection: Recessed Trims

R30 Regressed Eyeball Trim with Metal Baffle in White Finish

IC Airtight High Wattage: PAR-30L 75w, BR-30 65w, Non-IC:
 PAR-30L 75w, BR-30 65w, IC Airtight: PAR-30L 75w, BR-30 65w, IC
 Airtight Shallow: PAR-30L 75w, BR-30 65w

UPC #:785652110375

Finish: White (15)

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Frt. Class	UPS Ship
Individual	11037AT-15	1	785652110375	7.5	7.5	4.5	0.146	1.3	100	Yes
Master Pack		12	10785652110372	27	16	9	2.25	17.2	100	Yes
NJ Pallet		288		48	40	69	76.667	412.8		No
NV Pallet		288		48	40	69	76.667	412.8		No