

Eaton 1176V

Catalog Number: 1176V

Surge Protection Power Strip, Ivory, 4 in 14/3 SJT, 70J max, Thermoplastic, 5-15R, 7, Two-pole three-wire grounding, 125 Vac, 0° to 40°C



General specifications

Product Name	Catalog Number
Eaton circuit breaker switch power strip	1176V
UPC	Product Length/Depth
032664483202	2.25 in
Product Height	Product Width
15 in	3 in
Product Weight	Certifications
0.975 lb	cULus Listed NOM

Product specifications

Special features

Power surge strip

Cord type

4 in 14/3 SJT

Number of receptacles

7

Color

Ivory

Material

Thermoplastic

Number Of Poles

Two-pole

Type

Surge protection power strip

Joules

70J

NEMA configuration

5-15R

Device grade

COMMERCIAL

Operating temperature

0 to 40 °C

Number of wires

3

Receptacle type

Two-pole, three-wire, grounding

Voltage rating

125 V

Application

COMMERCIAL

Resources

Catalogs

[Arrow Hart Buyers Guide I-08](#)

Specifications and datasheets

[Eaton Specification Sheet - 1176V](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)