Elliott Electric Supply

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

1200 SW Door 15A 125/250vac

Pass & Seymour/Legrand

Catalog Number	1200
Manufacturer	Pass & Seymour/Legrand
Description	Pressure Sensitive Door and Canopy Switch, Pushbutton Actuator, 120/250 V Ac, 15 A, Wire Lead Connection, 1.516 In Overall Length, 1.547 In Overall Width, 4.031 In Overall Height, 30000 LM Operating Cycles, 1 Pole, Steel Housing Material, -30 °C Operating Temperature, +60 °C Operating Temperature, Wall Mount, 0.59 LB
Weight per unit	0.5860 (lbs/each)
Product Category	Hinge Switches & Accessories

Features

action	SP
actuator	Push Button
amperage rating	15
Contact Rating	120/250 VAC, 15 Amp
indoor/outdoor	Indoor
Load Rating	15 A @ 120/250 VAC
Load Type	Xenon, LED, Halogen, Fluorescent, Incandescent, CFL, Universal
Material	Thermoplastic
media	Yes
Number of Gangs	1
Number of Switches	1.0
Poles	1
Switch Type	Canopy
throw type	Single Throw
Voltage	250 VAC, 120 VAC
Wall Plate Included	NO
Wattage	Electrical power is expressed in Amps and Volts.
Wire Size	#14 - #10 Awg

Material, Color, and Finish

Finish	Matte

Dimensions and Weight

Height	4.031
Width	1.547

Descriptions

Description	SW DOOR 15A 125/250VAC
extra long description	P&S 1200 SW DOOR 15A 125/250VAC

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

GTIN	00785007120004
UPC	785007120004

Taxonomies, Classifications, and Categories

Category Description	Residential Switches
Type	Switch, Tamper-Resistant

Trade Size

Amperage	15.0

Packaging

Carton	1
Package	50
Weight Per each	0.586

Uses, Certifications, and Standards

environmental conditions	Flammability: UL94 V2
Mounting	WALL
standard	UL Listed