



CANOPY SWITCH

1200 | [Pass & Seymour](#)

FEATURES & BENEFITS

Pressure Sensitive Door & Canopy Switch, 15 Amp 120 Vac, 15 Amp 250 Vac

- Equipped with wire leads.
- 1200 and 1201 complete with metal box and plate.
- Only 14 oz. pressure actuates switch.
- Back box cold rolled steel.
- Plate is steel with a bronze coating.

SPECIFICATIONS

GENERAL INFO

Type: Pressure Sensitive Door & Canopy Switches

Number Of Poles: 1

Style: Decorator

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

cULus: Yes

UN SPSC: 39121507

DIMENSIONS

Depth (US): 1.547"

Height (US): 3.188"

Width (US): 1.516"

TECHNICAL INFORMATION

Amps: 15A

Volts: 120/250VAC

Volts (AC): 120

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant

